

**JAYCO SAFETY PRODUCTS PVT.  
LTD.**

**JS 11 ELECTRICAL HAND GLOVES**

SEAMLESS INSULATED TYPE

**TECHNICAL DATA SHEET - ELECTRO SAVIOUR BRAND**

**Product Information:**



1. Colour : OFF - WHITE
2. Weight : APPROX. 310 - 450 GMS
3. Palm Size : 10"
4. Length : 380 mm / 360 mm

**Type:** Seamless rubber insulated type

**Applications:**

Used for working in Electrical Works within the specified limits indicated on the bag & on each and every gloves and outer bag.

**As per I.S.13774:1993**

<b><u>Type</u></b>	<b><u>Testing potential</u></b>	<b><u>Working potential</u></b>
Class 00	2500 V	500 V
Class 0	5000 V	1000 V
Class 1	10000 V	7500 V
Class 2	20000 V	17000 V

**Technology:** Modern dipping technology with the moulds as per standards.

**Testing:**

1. Each and every gloves are tested for proof voltage in in-house laboratory. The certificate for the batch of 100 pairs will be provided.
2. Tested at ERDA - BARODA (GOVT. RECOGNOSIED).

**Fitting:** Special ergonomic design of mould with best dexterxity for better gripping.

**No Puncture:** Each and every pair is tested so no chance of puncture

**Warranty Information:**

Jayco Safety Products Pvt. Ltd warrants that it's Electro-saviour Gloves are free from defects in material and workmanship. This limited warranty does not cover any product or component found to have been altered, misused, abused, tampered with or improperly maintained or to have deteriorated due to ageing of any component made of rubber or any other elastomer. The limited warranty does not cover any damage, loss or expense due to damage caused by accident, abuse, improper maintenance, use or misuse of the product.

**Storage:**

Store in original packaging (Opaque packaging used for protection and instructions for use). Do not compact or fold. Do not expose to heat sources (sunlight, radiators, artificial light). Store between 10°C and 24°C.

**Inspection :**

Before each use, carry out a visual inspection. Any puncture or perforation makes the gloves unusable.

**Precautions :**

Do not expose to solvents or chemicals that may cause deterioration. Do not use the glove when damp.

**Cleaning :**

Use water and soap. Dry below 65°C with ambient humidity.

**Minimum packaging:**

1 pair. Opaque and single packaging used for protection and instructions for use. The Electro Saviour gloves, made of latex, are free of allergies ( process to clean off protein of latex). In case of allergic reaction to latex please do not use Electro Saviour gloves.

**Marking:**

The date of the electrical test made at the end of production is placed on every glove bag, as well as a lot number to ensure product traceability. Gloves that are used frequently should be tested at intervals less than 6 month. Gloves that are used only occasionally should be tested after each use and, in any case, at intervals of not more than 12 months. Gloves held in stock should be retested at intervals not exceeding 12 months

**Order information:** 50 pairs in each carton

**Carton Size (inches): 32 3/4 x 16 3/4 x 13 3/4**

**Contact Information:**