


Triad™ 36" (without Sequencer)


Seating Capacity.....	3-4 Adults
Dimensions	84" x 66" x 36", (213 cm x 168 cm x 91 cm)
Corner Radius.....	16" (41 cm)
Dry Weight.....	591 lbs (268 kg)
Filled Weight (Average Fill)	2,718 lbs (1,233 kg)
Water Capacity (Average Fill).....	255 US gallons (965 Liters)
Shipping Weight	591 lbs (268 kg)
Export Shipping Weight:.....	641 lbs (291 kg)
Electronic Controls	D1 SmartHUB™ full color glass touch control panel; access to control jets, temperature, settings and maintenance schedule
Pump 1.....	North America (60 Hz): 1-Speed, 3.6 HP break, 2.5 HP continuous, 48 Frame
Export (50 Hz):	1-Speed, 2.0 HP continuous
Pump 2.....	North America (60 Hz): 1-Speed, 3.6 HP break, 2.5 HP continuous, 48 Frame
Export (50 Hz):	1-Speed, 2.0 HP continuous
Circulation Pump.....	Yes
Fountain Pump	N/A
Filtration (factory default)	24/7 Filtration (Purge Cycles 2 x 10 minutes)
Total VCR Jets	33
Seat 1 Jets.....	2 Power Storm Multi-Port, 2 Cluster Storm Directional, 1 Typhoon (Footwell wall)
Seat 2 Jets.....	1 Pillow Mini Rotator, 2 Pillow Cluster Shower Directional, 4 Power Storm Rotator, 4 Power Storm Directional, 6 Mini Storm Rotator, 2 Mini Storm Directional
Seat 3 Jets.....	2 Power Storm Dual Rotator, 1 Power Storm Directional, 4 Mini Storm Directional, 2 Mini Storm Rotator
Massage Selectors	1
Special Features	Tactile Therapy, Spa Status Light, Flex Therapy Pillow™
Water Management System.....	UltraPure™ Plus System; Two 75 ft filter cartridge; 8" Weir
LED Lighting	Liquid FX™
Optional	Exterior Lights
Siena™ Cabinet Colors	Ashwood, Chestnut, Sandalwood
Acrylic Colors	Moonstone, UltraLife™, Sunstone, Smoked Marble, UltrLife Gray, Desert Stone
Headrests	2 (1 Standard, 1 Flex Therapy Pillow™)
Water Feature.....	N/A
Heater	2.1, 3.4, 5.5 kW
Export (50Hz)	2.1, 3.4, 5.5 kW
Electrical Requirements:	North America (60 Hz): 240 VAC@30A, 40A or 50A Export (50 Hz): 230 VAC@1x16A, 1x32A, 2x16A, 3x16A or suitably rated circuit breaker to comply with local electrical codes. Certain countries may require dual power inputs
Warranty*.....	North America (60 Hz): Lifetime for UltraLife Shell Surface, 7 Years Acrylic Shell Surface, 5 Years Plumbing, 5 Years Equipment and Controls, 7 Years for Cabinet, 1 Year Water Purification System, 2 Years for Jet Insert, 1 Year for Jet Escutcheon, 2 Years Lights, 1 Year Stereo; Export (50 Hz): 10 Years for UltraLife Shell Surface, 7 Years Acrylic Shell Surface, 5 Years Plumbing, 5 Years Equipment and Controls, 2 Years for Cabinet, 1 Year Water Purification System, 2 Years for Jet Insert, 1 Year for Jet Escutcheon, 2 Years Lights, 1 Year Stereo
Audio System (Optional).....	Fully Integrated Stereo System with Bluetooth capability, 4 premium speakers and a subwoofer
Optional	SmartTub®



*(See Warranty Document for Specific Details)

Triad 36" (without Sequencer)

Massage Selector Diagram




Spa Operation Subject to Change without Notice

Seat Depths

- 1 = 18.25" (46.36 cm)
- 2 = 10.25" (26.04 cm)
- 3 = 26.00" (66.04 cm)
- 4 = 26.25" (66.68 cm)
- 5 = 34.00" (86.36 cm)


Listed dimensions represent distance from top of acrylic to lowest point in seat. **Tolerance $\pm 0.5"$ (1.27 cm).**



Dimensions/Specifications are Subject to Change Without Notice

Triad 36" (without Sequencer)

Jet Designation



Dimensions/Operation/Specifications are Subject to Change Without Notice


33 Total Jets



Total Jets




Triad 36" (without Sequencer)



*Caution:

Due to manufacturing tolerances there could be some minor differences between the actual spa and the drawing above.

If site planning is critical to such tolerances, be sure to measure your actual spa.



- Note:**
1. Engineering specs may differ slightly from brochure.
 2. For lifter installation allow 18" (45.7cm) clearance on the backside of the spa.
 3. Alternative cabinets may add significant weight. Ask your dealer for exact details
 4. This is the approximate location for drilling a hole if you must bring the power line in through the bottom of the spa. Be careful not to puncture a plumbing line inside the equipment compartment (drill from the inside compartment out).

Dimensions/Specifications are Subject to Change Without Notice (Tolerance $\pm 0.5"$ [1.27 cm]).